

**JA80 PARTS**



**J14HV840 & Accessories**

- | **JA80**

**Swing Arm Mount**

- | **JM80**

**JA80 SWING ARM**

**Healthcare Articulating Swing Arm for Personal TVs**

The RCA JA80 Swing Arm was made to support the J14HV840 RCA Personal TV & works well with most other personal television systems. The internal braking system ensures that the arm stays put. The powdered finish is easy to clean, and the low profile hardware is attractive and less likely to catch on any clothing, bedding or instruments. The optional arm halo provides 360° protection, and allows the TV & Arm to be moved without putting stress on the TV unit. The J14HV840 flexible braided coaxial cable increases the life expectancy, reducing long term cost.

**Specifications**

Maximum Reach	Up to 57"
Minimum Ceiling Clearance	30"
Minimum Floor Clearance	47 ± 2"
Weight (lbs.)	15 lbs
Load Limit	6 lbs
Shipping Size ( W x H x D )	18" x 29" x 4"
Shipping Weight (lbs.)	19 lbs.
UPC	811635020925

**DESIGNED FOR USE IN**



**Hospital Rooms**

Healthcare UL Listed, powder coated finish makes the JA80 arm, and personal TV system ideal for hospital rooms.



**Dialysis Centers**


JA80 articulating arm allows patients to pull their personal TV close for viewing that does not disturb neighboring patients.

# SPECIFICATIONS

# HV SERIES

## JA80 Arm & Mounting System

- | **JA80 Hospital Grade Swing Arm** that extends up to 57" Inches.
- | **Smooth Motion** build that makes maneuvering the swing arm to a comfortable viewing position for any patient.
- | **Protective Halo** (included) to provide 360° protection for your TV.
- | **JM80** mount works with the JA80 arm to provide 180° range of motion.




## JA80 Accessories



### JM80

#### Wall Mount

The JM80 is an optional part of the J14HV840 Healthcare TV System. This mount secures directly to the wall, and pairs with the JA80 arm to provide 180° range of motion.



### Protective Halo

#### Included with JA80 Arm

Every JA80 swing arm includes a protective halo in the shipping package. 14.5 inches in diameter, the halo can be used to provide 360° of protection to your television. It also doubles as a way to move the swing arm, without putting pressure on the television.